



PRODUCT DATA SHEET

Polystyrene Particles-SO3H

Description

Abvigen has developed a large selection of polystyrene micro- and nanoparticles. Polystyrene particles and Microparticles are highly spherical plastic particles in sizes between 1 μm to 100 μm . The polystyrene particles are prepared by using emulsion polymerization process. Coated or conjugated particles are prepared either by passive adsorption or covalent coupling.

For custom sizes, formulations or bulk quantities please contact our customer service department.

website: www.abvigen.com Phone: +1 929-202-3014 Email: info@abvigenus.com

Characteristics

Core diameter: 1 μm to 100 μm

Size: 10 ml; 20 ml; 50 ml; 100 ml

Shape: Spherical

Concentration: 50 mg/ml

Density: 1.03 g/ccm

Composition: Polystyrene Particles

Buffer: DI Water

Form: Suspension

Colour: White

Storage

This product should be stored at 4°C. **DO NOT FREEZE.** If stored unopened and as specified, Abvigen

Polystyrene Particles are stable for at least 12 months.

Highlights

Superior size distribution compared to the leading competitor

Available from 1 μm to 100 μm

Size Standards

Exceptional protein binding characteristics

1378 US-206 Ste 6-126, Skillman, NJ USA

Email: info@abvigenus.com

Tel: 1-816-388- 0112 Fax: 1- 888-616-0161

© Abvigen Inc All Rights Reserved



Available with multiple surface functionalities to suit all your needs

NPS of Polystyrene particles, 50 mg/ml

Diameter	Conc. mg/ml	Particles/mg	Particles/ml	Diameter	Conc. mg/ml	Particles/mg	Particles/ml
25 nm	50	1.19E+14	1.19E+15	10 um	50	1.85E+06	1.85E+07
50 nm	50	1.48E+13	1.48E+14	20 um	50	2.32E+05	2.32E+06
100 nm	50	1.85E+12	1.85E+13	30 um	50	6.87E+04	6.87E+05
200 nm	50	2.32E+11	2.32E+12	40 um	50	2.90E+04	2.90E+05
300 nm	50	6.87E+10	6.87E+11	50 um	50	1.48E+04	1.48E+05
400 nm	50	2.90E+10	2.90E+11	60 um	50	8.58E+03	8.58E+04
500 nm	50	1.48E+10	1.48E+11	70 um	50	5.41E+03	5.41E+04
600 nm	50	8.58E+09	8.58E+10	80 um	50	3.62E+03	3.62E+04
700 nm	50	5.41E+09	5.41E+10	90 um	50	2.54E+03	2.54E+04
800 nm	50	3.62E+09	3.62E+10	100 um	50	1.85E+03	1.85E+04
900 nm	50	2.54E+09	2.54E+10	200 um	50	2.32E+02	2.32E+03
1 um	50	1.85E+09	1.85E+10	300 um	50	6.87E+01	6.87E+02
2 um	50	2.32E+08	2.32E+09	400 um	50	2.90E+01	2.90E+02
3 um	50	6.87E+07	6.87E+08	500 um	50	1.48E+01	1.48E+02
4 um	50	2.90E+07	2.90E+08	600 um	50	8.58E+00	8.58E+01
5 um	50	1.48E+07	1.48E+08	700 um	50	5.41E+00	5.41E+01
6 um	50	8.58E+06	8.58E+07	800 um	50	3.62E+00	3.62E+01
7 um	50	5.41E+06	5.41E+07	900 um	50	2.54E+00	2.54E+01
8 um	50	3.62E+06	3.62E+07	1 mm	50	1.85E+00	1.85E+01
9 um	50	2.54E+06	2.54E+07	3 mm	50	6.87E-02	6.87E-01

Polystyrene Particles Centrifugation Parameters

Particle Size	Centrifugal Acceleration	Time	Resuspension of Pellet
50 nm	45,000 x g	30 min	30 min sonication / vortex
100 nm	45,000 x g	30 min	30 min sonication / vortex


1378 US-206 Ste 6-126, Skillman, NJ USA

Email: info@abvigenus.com


Tel: 1-816-388- 0112 Fax: 1- 888-616-0161

© Abvigen Inc All Rights Reserved


200 nm	45,000 x g	30 min	30 min sonication / vortex
500 nm	45,000 x g	20 min	10 min sonication / vortex
800 nm	10,000 x g	20 min	10 min sonication / vortex
1 μ m	3,500 x g	15 min	10 min sonication / vortex
2 – 4 μ m	1,600 x g	15 min	vortex
5 - 8 μ m	1,200 x g	10 min	vortex
> 8 μ m	25 x g	10 min	vortex




20 nm




300 nm




1 um



500 nm



5 um



10 um

Ordering Information

website: www.abvigen.com

Phone: +1 929-202-3014

Email: info@abvigenus.com

1378 US-206 Ste 6-126, Skillman, NJ USA

Email: info@abvigenus.com

Tel: 1-816-388- 0112 Fax: 1- 888-616-0161

© Abvigen Inc All Rights Reserved