



Polystyrene Particles-CHO PRODUCT DATA SHEET

Polystyrene Particle-CHO

Description

Abvigen has developed a large selection of polystyrene micro- and nanoparticles. Polystyrene particles and Microparticles are highly spherical plastic particles in sizes between 20 nm to 3 mm. The polystyrene particles are prepared by using emulsion polymerization process. Coated or conjugated particles are prepared either by passive adsorption or covalent coupling.

For custom sizes, formulations or bulk quantities please contact our customer service department.

website: www.abvigen.com Phone: +1 929-202-3014 Email: info@abvigenus.com

Characteristics

Core diameter: 50 nm -100 um

Size: 10 ml; 20 ml; 50 ml; 100 ml

Concentration: 25 mg/ml

Shape: Spherical

Density: 1.03 g/ccm

Composition: Polystyrene Particles

Functional Group: CHO

Buffer: DI Water

Form: Suspension

Colour: White

Store: Storage at 2 - 8 °C

Storage

This product should be stored at 4°C. **DO NOT FREEZE.**

Highlights

Superior size distribution compared to the leading competitor; available from 20 nm to 100 um

1378 US-206 Ste 6-126, Skillman, NJ USA

Email:

info@abvigenus.com

Tel: 1-816-388- 0112 Fax: 1- 888-616-0161

© Abvigen Inc All Rights

Reserved



Size Standards

Exceptional protein binding characteristics

Available with multiple surface functionalities to suit all your needs

For 25 mg/ml of Polystyrene Particles

Diameter	Conc. mg/ml	Particles/mg	Particles/ml	Diameter	Conc. mg/ml	Particles/mg	Particles/ml
25 nm	25	1.19E+14	2.97E+15	10 um	25	1.85E+06	4.64E+07
50 nm	25	1.48E+13	3.71E+14	20 um	25	2.32E+05	5.79E+06
100 nm	25	1.85E+12	4.64E+13	30 um	25	6.87E+04	1.72E+06
200 nm	25	2.32E+11	5.79E+12	40 um	25	2.90E+04	7.24E+05
300 nm	25	6.87E+10	1.72E+12	50 um	25	1.48E+04	3.71E+05
400 nm	25	2.90E+10	7.24E+11	60 um	25	8.58E+03	2.15E+05
500 nm	25	1.48E+10	3.71E+11	70 um	25	5.41E+03	1.35E+05
600 nm	25	8.58E+09	2.15E+11	80 um	25	3.62E+03	9.05E+04
700 nm	25	5.41E+09	1.35E+11	90 um	25	2.54E+03	6.36E+04
800 nm	25	3.62E+09	9.05E+10	100 um	25	1.85E+03	4.64E+04
900 nm	25	2.54E+09	6.36E+10	200 um	25	2.32E+02	5.79E+03
1 um	25	1.85E+09	4.64E+10	300 um	25	6.87E+01	1.72E+03
2 um	25	2.32E+08	5.79E+09	400 um	25	2.90E+01	7.24E+02
3 um	25	6.87E+07	1.72E+09	500 um	25	1.48E+01	3.71E+02
4 um	25	2.90E+07	7.24E+08	600 um	25	8.58E+00	2.15E+02
5 um	25	1.48E+07	3.71E+08	700 um	25	5.41E+00	1.35E+02
6 um	25	8.58E+06	2.15E+08	800 um	25	3.62E+00	9.05E+01
7 um	25	5.41E+06	1.35E+08	900 um	25	2.54E+00	6.36E+01
8 um	25	3.62E+06	9.05E+07	1 mm	25	1.85E+00	4.64E+01
9 um	25	2.54E+06	6.36E+07	3 mm	25	6.87E-02	1.72E+00

Polystyrene Particles Centrifugation Parameters

Particle Size	Centrifugal Acceleration	Time	Resuspension of Pellet
50 nm	45,000 x g	30 min	30 min sonication / vortex

1378 US-206 Ste 6-126, Skillman, NJ USA

Email:

info@abvigenus.com

Tel: 1-816-388- 0112 Fax: 1- 888-616-0161

© Abvigen Inc All Rights

Reserved



100 nm	45,000 x g	30 min	30 min sonication / vortex
200 nm	45,000 x g	30 min	30 min sonication / vortex
500 nm	45,000 x g	20 min	10 min sonication / vortex
800 nm	10,000 x g	20 min	10 min sonication / vortex
1 μ m	3,500 x g	15 min	10 min sonication / vortex
2 – 4 μ m	1,600 x g	15 min	vortex
5 - 8 μ m	1,200 x g	10 min	vortex
> 8 μ m	25 x g	10 min	vortex

Ordering Information

website: www.abvigen.com

Phone: +1 929-202-3014

Email: info@abvigenus.com

1378 US-206 Ste 6-126, Skillman, NJ USA

info@abvigenus.com

Tel: 1-816-388- 0112 Fax: 1- 888-616-0161

Reserved

Email:

© Abvigen Inc All Rights